

Here are the connections for the P48 High Z buffer for Piezo hydrophones

The outside silver plating goes to “SGNL”.
The inside silver plating is connected to “GND”.

With P48 applied:
TP1 = 11.5-12VDC
TP2 = 11.3-11.8VDC
XLR_2 and XLR_3 = 20-22VDC
AGND 5.3-5.7V

This circuit is suitable for any piezo pickup or contact microphone. For contact microphones, ensure you use adequate shielding.

NOTE: Pay attention to XLR Pin Numbers. They are printed on most connectors. Look Closely

